

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush with shank Steel wire 0.30 mm, Brush Ø D1× bristle width L1:
40X10mm****Order data**

Order number	574000 40X10
GTIN	4017359037409
Item class	57L

Description**Version:**

Waved special high quality wire, **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

Technical description

Brush Ø D ₁	40 mm
Bristle thickness	0.3 mm
Length of brush section H ₁	9 mm
maximum speed	18000 min ⁻¹
Bristle width L ₁	10 mm
Shank Ø D _s	6 mm

Brush material	Steel wire
Twisted knotting	waved
Type of product	Wheel brush