

**LESSMANN®**  
THE GERMAN BRUSH COMPANY

## Wheel brush with shank knotted steel wire 0.50 mm, Type: 75X10



### Order data

Order number	574400 75X10
GTIN	4017359007266
Item class	57L

### Description

**Version:**

Knotted steel wire, **shank Ø 6 mm.**

**Application:**

Very aggressive brushing effect with high wear resistance. For removal of rust, scale and burrs.

### Technical description

Bristle thickness	0.5 mm
Length of brush section H <sub>1</sub>	15 mm
Brush Ø D <sub>1</sub>	75 mm
Number of twisted knots	18
maximum speed	25000 min <sup>-1</sup>
Bristle width L <sub>1</sub>	12 mm
Shank Ø D <sub>s</sub>	6 mm
Brush material	Steel wire

Twisted knotting	left knotted
Type of product	Wheel brush