



## Combination spanner, chrome-plated, Width across flats: 24mm



### Order data

Order number	613950 24
GTIN	4045197159885
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw width.  
With oval shaft.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 280 mm

maximum jaw height h<sub>1</sub>: 12 mm

maximum ring height h<sub>2 max</sub>: 16 mm

### Technical description

Width across flats	24 mm
maximum jaw height h <sub>1</sub>	12 mm
Spanner length L	280 mm
Width across flats	metric
maximum ring height h <sub>2 max</sub>	16 mm
Standard	DIN 3113 A
Standard	ISO 3318
Standard	ISO 7738
Ring setting	15 °

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner