



## Combination spanner, chrome-plated, Width across flats: 27mm



### Order data

Order number	613950 27
GTIN	4045197159892
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw width.  
With oval shaft.

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

maximum jaw height h1	13 mm
Spanner length L	310 mm
Width across flats	27 mm
Width across flats	metric
maximum ring height h <sub>2max</sub>	18 mm
Standard	DIN 3113 A
Standard	ISO 3318
Standard	ISO 7738
Ring setting	15 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner