



Combination spanner, long version, Width across flats: 17mm



Order data

Order number	614200 17
GTIN	4018754019250
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw width.

With easy-grip fluted shaft. Optimum flex resistance, good torque transmission.

Standard:

DIN 3113 B / ISO 3318 / ISO 7738

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Note:

AS-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 614600

Technical description

Ring end AS drive	yes
maximum jaw height h ₁	8 mm
Width across flats	17 mm
Spanner length L	240 mm
Width across flats	metric
maximum ring height h _{2 max}	12 mm

Ring setting	15 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated over nickel
Type of product	Spanner