

**TESA****Contact point interface****Order data**

Order number	434719
GTIN	7630041115246
Item class	45C

Description**Version:**

Interface for data transmission and management of measuring instruments. Facility for direct connection to an USB interface.

- **Facility for inputting limit values. Simple Functions + A, -A, + A + B + A-B. Data export in.csv format.**
- **Facility for connection of up to 64 probes by USB serial connection of multiple interfaces.**
- **Measurement signal input from TESA measuring probes.**
- **Measurement signal output digital RS232.**
- **Measurement range selectable: 2 mm, 5 mm.**

Application:

For centralised process monitoring and control of measuring equipment at multiple locations in measurement chains.

Supplied with:

TIS software

Interface: RS232C interface

Interface: USB interface

Length: 172 mm

Width: 155 mm

Height: 55 mm

Technical description

Height	55 mm
Width	155 mm
Length	172 mm
Interface	RS232C interface
Interface	USB interface
Type of product	Interface box

Services

Labelling laser-etched Type	018940
-----------------------------	--------