



Combination spanner, long version, Width across flats: 34mm



Order data

| | |
|--------------|---------------|
| Order number | 614200 34 |
| GTIN | 4018754019397 |
| Item class | 63A |

Description

Version:

Drop-forged. With close tolerance jaw width.

With easy-grip fluted shaft. Optimum flex resistance, good torque transmission.

Standard:

DIN 3113 B / ISO 3318 / ISO 7738

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Note:

AS-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 614600

Technical description

| | |
|----------------------------------------|--------|
| Spanner length L | 460 mm |
| Ring end AS drive | yes |
| maximum jaw height h ₁ | 13 mm |
| Width across flats | 34 mm |
| Width across flats | metric |
| maximum ring height h _{2 max} | 18 mm |

| | |
|-----------------------|---------------------------|
| Ring setting | 15 degrees |
| Manufacturing process | drop forged |
| Material | Chrome alloy steel |
| Surface | chrome-plated over nickel |
| Type of product | Spanner |