

**Cordless impact wrench / impact driver, Type: GDS12115****Order data**

| | |
|--------------|-----------------|
| Order number | 074054 GDS12115 |
| GTIN | 3165140910705 |
| Item class | 03B |

Description**Version:**

Cordless impact wrench / impact driver.

- **Reversible.**
- **Battery charge display.**
- **Compact impact screwdrivers for high precision.**
- **Perfect handling thanks to the short overall length.**
- **Higher precision: 2-stage power control to avoid overdriving smaller screws.**
- **Longer motor life thanks to brushless EC motor technology.**
- **LED light for illuminating the working area, even in dark areas.**

Advantage:

Perfect handling thanks to the short overall length.

Supplied with:

Supplied with 2 × Li-ion rechargeable batteries, charger, L-BOXX.

Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073859.

Technical description

| | |
|---------------------|--------|
| maximum torque hard | 115 Nm |
|---------------------|--------|

| | |
|--|------------------------------|
| Weight | 0.9 kg |
| Number of impacts | 0 - 3100 min ⁻¹ |
| Tool arbor size | 3/8 in |
| Tool arbor drive profile | External square drive |
| Battery capacity | 3 Ah |
| maximum speed 2nd speed | 2600 min ⁻¹ |
| Manufacturer's designation | GDS 12V-115 |
| maximum speed 1st speed | 1200 min ⁻¹ |
| maximum screw Ø (8.8 - 12.9) | M12 |
| suitable battery - supplier / battery type / voltage | Bosch 12 V |
| Battery voltage | 12 V |
| typical application | Strong |
| Packaging | Modular case (L-Boxx) |
| maximum vibration to EN | 10 m/s ² |
| Number of rechargeable batteries contained | 2 |
| Type of rechargeable battery | Lithium-ion |
| Power supply | Rechargeable battery-powered |
| Suitable for material | Steel |
| Type of product | Impact wrench |

Accessories

| | |
|--|------------|
| Li-ion battery Battery type, battery voltage B12 V | 073855 B12 |
|--|------------|