

**Cordless impact wrench / impact driver, Type: GDR12110****Order data**

Order number	074054 GDR12110
GTIN	3165140910682
Item class	03B

**Description****Version:**

Cordless impact wrench / impact driver.

- **Reversible.**
- **Battery charge display.**
- **Compact impact screwdrivers for high precision.**
- **Perfect handling thanks to the short overall length.**
- **Higher precision: 2-stage power control to avoid overdriving smaller screws.**
- **Longer motor life thanks to brushless EC motor technology.**
- **LED light for illuminating the working area, even in dark areas.**

**Advantage:**

Perfect handling thanks to the short overall length.

**Supplied with:**

Supplied with 2 × Li-ion rechargeable batteries, charger, L-BOXX.

**Note:**

Suitable replacement batteries and chargers can be found under No. 073851 – 073859.

**Technical description**

maximum speed 2nd speed	2600 min <sup>-1</sup>
-------------------------	------------------------

Weight	0.9 kg
suitable battery - supplier / battery type / voltage	Bosch 12 V
Tool arbor size	1/4 in
Number of impacts	0 - 3100 min <sup>-1</sup>
maximum torque hard	110 Nm
Packaging	Modular case (L-Boxx)
Manufacturer's designation	GDR 12V-110
Battery voltage	12 V
maximum vibration to EN	10 m/s <sup>2</sup>
Tool arbor drive profile	Internal square drive
typical application	Strong
maximum screw Ø (8.8 - 12.9)	M12
Battery capacity	3 Ah
maximum speed 1st speed	1200 min <sup>-1</sup>
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

## Accessories

Li-ion battery Battery type, battery voltage B12 V	073855 B12
--	------------