

**Cordless special drill / driver, Type: GWB1210****Order data**

| | |
|--------------|----------------|
| Order number | 070223 GWB1210 |
| GTIN | 3165140730846 |
| Item class | 03B |

Description**Version:****Bosch – cordless right angle drill**

- **Bosch premium lithium-ion technology.**
- **Battery charge display.**
- **Very compact: short, 5-way adjustable head with 10 mm auto-lock drill chuck.**
- **High speed from 0-1300 rpm for fast work progress – optimal for holes, motor brake.**

Advantage:

For inaccessible places.

Supplied with:

Including charger, L-BOXX 102, 1/2 L-BOXX inlay for accessories, 1/2 L-BOXX inlay for device.

Note:

See from No. 073851 and No. 073866 for suitable replacement batteries and chargers.

Technical description

| | |
|----------------------------|----------------------------|
| Battery voltage | 12 V |
| Battery capacity | 2 Ah |
| Toolholder | Ø 1.0 – 10 mm |
| Packaging | Modular case (L-Boxx) |
| Manufacturer's designation | GWB1210 |
| maximum torque hard | 11 Nm |
| maximum speed 1st speed | 0 - 1300 min ⁻¹ |

| | |
|--|------------------------------|
| maximum twist drill size Ø in steel | 10 mm |
| Format | Right angle drill / driver |
| Weight | 1.2 kg |
| typical application | Medium |
| maximum twist drill size Ø in wood | 10 mm |
| suitable battery - supplier / battery type / voltage | Bosch 12 V |
| Type of rechargeable battery | Lithium-ion |
| Number of rechargeable batteries contained | 2 |
| Power supply | Rechargeable battery-powered |
| Suitable for material | Concrete |
| Suitable for material | Steel |
| Suitable for material | Masonry |
| Type of product | Screwdriver |

Accessories

| | |
|--|------------|
| Li-ion battery Battery type, battery voltage B12 V | 073851 B12 |
|--|------------|