



Cordless special drill / driver, Type: M12IR3/8

Order data

Order number	070228 M12IR3/8
GTIN	4002395002023
Item class	03L

Description

Version:

MILWAUKEE – cordless right angle drill / driver and ratchet driver

- **REDLINK™ electronics with stepless speed control, reversible running and overload protection.**
- **LED illumination of the working area.**
- **Red Li-ion batteries with single-cell monitoring and charge display.**

Slim and sturdy ratchet screwdriver with torque up to 47 Nm. Reinforced casing for long working life. Very compact – **only 45 mm Ø handle.**

With **3/8"** square toolholder.

Supplied with:

1× 12 V / 2.0 Ah Red Li-ion batteries, charger, transport bag.

Note:

See No. 073814 ff. and No. 073840 for suitable spare batteries and chargers.

suitable battery - supplier / battery type / voltage: Milwaukee type B 12 V

Manufacturer's designation: M12 IR (3/8")

Battery voltage: 12 V

Battery capacity: 2 A·h

maximum torque hard: 47 N·m

maximum speed 1st speed: 0 - 250 rpm

Toolholder: Square 3/8"

Technical description

Type of rechargeable battery

Type of product

