

AEG

Cordless drill / driver, Type: BS18C2

Order data

Order number	070222 BS18C2
GTIN	4002395135677
Item class	07A

Description

Version:

AEG – Cordless drill / driver

- **Sturdy and handy cordless 2-speed drill / screwdriver, reversible.**
- **FIXTEC quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **23-step torque limit adjustment, plus drill steps.**
- **13 mm quick-change chuck.**
- **4-pole motor for maximum power within a compact design.**

Standard:

- **Sturdy and handy cordless 2-speed drill / driver, reversible.**
- **FIXTEC quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**

Supplied with:

2× 18 V / 2.0 Ah Li-ion batteries, charger, transport case and additional handle.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073820ff and No. 073841 for suitable spare batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: AEG type B 18 V

Manufacturer's designation: BS 18 CLI

Motor design: 4-pole motor

Battery voltage: 18 V

Battery capacity: 2 A·h

maximum torque hard: 60 N·m

maximum speed 1st speed: 0 - 450 rpm

Technical description

Type of product
