

**Cordless pop rivet tool PowerBird® Pro****Order data**

Order number	770507
GTIN	4007081942706
Item class	74A

Description**Version:**

Cordless tool for flexible use.

Advantage:

High operating speed combined with equally high performance; high reliability due to electronic control.

Supplied with:

Includes Li-ion push-in battery No. 770529 and charger No. 770528 size 2 in a plastic case.

Nozzles 17 / 32, 17 / 36, 17 / 40 and 17 / 45.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Tool stroke: 25 mm

for pop rivets in all materials up to: 6.4 mm

Setting force: 15000 N

Battery capacity: 18 A·h

Battery voltage: 2.1 V

Weight including rechargeable battery: 2 kg

Technical description

Tool stroke	25 mm
-------------	-------

Setting force	15000 N
for pop rivets in all materials up to	6.4 mm
Weight including rechargeable battery	2 kg
Battery capacity	18 A·h
Battery voltage	2.1 V

Accessories

Li-ion quick-change battery Capacitance 2,1 A·h	770529 2,1
Battery charger Type 2	770528 2