



Cordless 4-speed drill / driver, Manufacturer ID: 71161061

Order data

| | |
|--------------|-----------------|
| Order number | 070204 71161061 |
| GTIN | 4014586881447 |
| Item class | 03F |

Description

Version:

Cordless drill / driver

- For precise drilling and screw tightening results.
 - Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
 - Sturdy metal gearbox for long working life.
 - Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
 - Li-ion batteries with high current capability, single-cell monitoring, and capacity display.
- Powerful 12V cordless screwdriver with brushless motor with 4-speed gearbox and removable drill chuck.**
- Brushless FEIN power drive motor, powerful and maintenance-free for maximum efficiency and working life.
 - QuickIN quick-change system.
 - Removable drill chuck in all-metal design for outstanding load capacity under the toughest conditions.
 - Optimum cutting speed for every drill diameter, thanks to 4-speed all-metal gearbox.
 - Drill 6 mm holes in metal in 4th gear at 2500 rpm.
 - Powerful thread tapping in 1st gear.
 - Optimum speeds for self-tapping screws, stepped drills or the thread tapping.
 - Compact 150 mm long (without drill chuck).
 - FEIN SafetyCell Technology. Protects the battery and the machine against overheating and deep discharge.
 - Maintenance-free, brushless EC motor with 30 % higher efficiency than DC motors, and high speed stability.
 - Very low wear and up to 10 times the working life compared to standard DC motors.
 - Patented 4-speed gearbox with direct drive for positive screw tightening, drilling at optimised speed, and for thread tapping.

Mechanical torque cut-out adjustable in 20 steps, additional drilling step. **Mechanical torque cut-out** adjustable in 20 steps, additional drilling step.

Supplied with:

2 x 12V / 2.5 Ah Li-ion batteries, drill chuck, charger, waist clip, transport case.

Note:

See No. 073832 ff. for suitable starter kits, spare batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 12 V

Manufacturer's designation: ASCM 12QC

Battery voltage: 12 V

Battery capacity: 2.5 A·h

maximum torque soft: 20 N·m

maximum torque hard: 40 N·m

maximum speed 1st speed: 400 rpm

Technical description

Type of product
