



## Cordless 4-speed drill / driver, Manufacturer ID: 71161161

### Order data

Order number	070200 71161161
GTIN	4014586887456
Item class	03F

### Description

#### Version:

#### Cordless drill / driver

- For precise drilling and screw tightening results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Li-ion batteries with high current capability, single-cell monitoring, and capacity display.

#### Cordless 4-speed drill / driver with brushless EC motor

- Extremely powerful drill / driver with high concentricity.
- Maintenance-free brushless EC motor with 30% higher efficiency than DC motors, and high speed stability.
- Very low wear and up to 10 times the working life of standard DC motors.
- The high efficiency and the increased battery capacity permit up to 50 % longer operating times.
- Patented 4-speed gearbox with direct drive for positive screw tightening, drilling at optimised speed, together with thread tapping.
- Multi-stage torque setting adjustable in 15 steps, additional drilling step.

With removable **QuickIN quick-change drill chuck** and **carbide-coated jaws**.

#### Supplied with:

2× 18 V Li-ion batteries, drill chuck, charger, belt clip, transport case.

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB.

#### Note:

See No. 073834 ff and 073845 for suitable spare batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: ASCM 18 QM

Battery voltage: 18 V

Battery capacity: 5 A·h

maximum torque soft: 46 N·m  
maximum torque hard: 90 N·m  
maximum speed 1st speed: 400 rpm

---

## Technical description

Type of product

---