

**Cordless drill/driver, Type: 71132264****Order data**

Order number	070205 71132264
GTIN	4014586887203
Item class	03F

Description**Version:****2 and 4 speed cordless drill/driver**

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

2-speed cordless impact drill / driver with brushless motor.

- Low-maintenance, POWER-Drive EC motor with high torque, and overload protection.
- Mechanical stage torque setting, adjustable in 22 steps, additional drilling step.
- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.

- **Li-ion batteries with high current capability, single-cell monitoring, and capacity display.**

Advantage:

Mechanical torque setting.

Supplied with:

Supplied with battery and charger. Supplied with drill chuck, belt clip and transport case.

Without battery and without charger.

Technical description

Weight	3.7 kg
maximum torque hard	60 Nm
maximum speed 1st speed	450 - 450 min ⁻¹
Quick-clamping chuck range	1.5 - 13 mm
Motor design	Brushless motor
Battery voltage	18 V
maximum twist drill size Ø in wood	50 mm
typical application	Strong
maximum twist drill size Ø in steel	13 mm
Packaging	Carrying case
maximum torque soft	32 Nm
suitable battery - supplier / battery type / voltage	Fein type E 18 V
maximum speed 2nd speed	2000 min ⁻¹
Manufacturer's designation	ABS 18Q Select
maximum vibration to EN	<2.5 m/s ²
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver
USP1	18V, 2-speed

USP2

Quick-release chuck clamping
range 1.5-13, in a carrying case

Accessories

Li-ion battery Rechargeable battery type, battery voltage
FE18 V

073837 FE18