



## Cordless drill/driver without rechargeable battery and charger, Type: 71161164



### Order data

Order number	070200 71161164
GTIN	4014586887340
Item class	03F

### Description

#### Version:

#### 2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

#### Advantage:

With QuickIN MAX interface.

#### Supplied with:

Without battery and charger. Supplied with drill chuck, belt clip and transport case. **Without battery and without charger.**

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB.

**Note:**

See No. 073851 – 073866 for suitable batteries, chargers and starter sets.

## Technical description

maximum speed 2nd speed	800 min <sup>-1</sup>
maximum torque soft	45 Nm
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Manufacturer's designation	ASCM 18 QMSelect
maximum twist drill size Ø in wood	50 mm
Packaging	Carrying case
maximum torque hard	90 Nm
Battery voltage	18 V
maximum speed 4th speed	3850 min <sup>-1</sup>
Quick-clamping chuck range	1.5 - 13 mm
Motor design	Brushless motor
typical application	Heavy Duty
maximum vibration to EN	<2.5 m/s <sup>2</sup>
maximum twist drill size Ø in steel	25 mm
maximum speed 1st speed	400 - 400 min <sup>-1</sup>
maximum speed 3rd speed	1950 min <sup>-1</sup>
Weight	1.5 kg
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/driver
USP1	4-speed gearbox. 18V

USP2

Suitable for wood & steel, quick-release chuck clamping range 1.5-13, without rechargeable battery

---

## Accessories

Li-ion battery Rechargeable battery type, battery voltage FE18 V

073835 FE18