

**Cordless drill / driver, Manufacturer ID: GSR1215****Order data**

| | |
|--------------|----------------|
| Order number | 070240 GSR1215 |
| GTIN | 3165140727495 |
| Item class | 03B |

Description**Version:**

Bosch cordless drill / driver

- **Compact, powerful 12 V cordless drill with forward/reverse operation.**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Supplied with:

2x 12 V / 2 Ah Li-ion batteries, charger, transport case.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073852 ff and 073866 for suitable spare batteries and chargers.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 12 V

Manufacturer's designation: GSR 12V-15

Motor design: 2-pole motor

Battery voltage: 12 V

Battery capacity: 2 A·h

maximum torque soft: 15 N·m
maximum torque hard: 30 N·m

Technical description

| | |
|--|------------------------|
| Speed range 2nd speed | 0 - 1300 rpm |
| maximum torque soft | 15 N·m |
| Weight | 1 kg |
| typical application | Medium |
| Speed range 1st speed | 0 - 380 rpm |
| maximum vibration to EN | < 2.5 m/s ² |
| Manufacturer ID | GSR1215 |
| Manufacturer's designation | GSR 12V-15 |
| Battery voltage | 12 V |
| Packaging | Modular case (L-Boxx) |
| Motor design | 2-pole motor |
| maximum twist drill size Ø in wood | 19 mm |
| maximum torque hard | 30 N·m |
| Battery capacity | 2 A·h |
| Quick-clamping chuck range | 0 - 10 mm |
| suitable battery - supplier / battery type / voltage | Bosch 12 V |
| maximum twist drill size Ø in steel | 10 mm |
| Number of rechargeable batteries contained | 2 |
| Battery type | Lithium-ion |

Accessories

| | |
|---|-----------------|
| Li-ion battery Battery type, battery voltage B12 V | 073851 B12 |
| Battery charger Manufacturer's designation AL1130CV | 073866 AL1130CV |