



Combination spanner set, long version, Number of keys: 11



Order data

Order number	614210 11
GTIN	4018754058341
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw width.

With easy-grip fluted shaft. Optimum flex resistance, good torque transmission.

Standard:

DIN 3113 B / ISO 3318 / ISO 7738

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Supplied with:

1 each combination spanner No. 614600 / 614200 / 614900: Size 10; 13; 16; 17; 18; 19; 21; 22; 24; 27; 30

Note:

AS-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

Number of keys	11
Ring end AS drive	yes
Width across flats	metric

Type of product	Spanner
-----------------	---------

Accessories

Combination spanner, long version Width across flats 19 mm	614200 19
--	-----------

Combination spanner, long version Width across flats 24 mm	614200 24
--	-----------

Combination spanner, long version Width across flats 16 mm	614200 16
--	-----------

Combination spanner, long version Width across flats 22 mm	614200 22
--	-----------

Combination spanner, long version Width across flats 13 mm	614200 13
--	-----------

Combination spanner, long version Width across flats 17 mm	614200 17
--	-----------

Combination spanner, long version Width across flats 10 mm	614200 10
--	-----------

Combination spanner, long version Width across flats 21 mm	614200 21
--	-----------

Combination spanner, long version Width across flats 18 mm	614200 18
--	-----------

Combination spanner, long version Width across flats 27 mm	614200 27
--	-----------

Combination spanner, long version Width across flats 30 mm	614200 30
--	-----------