

MIRKA**Compact cordless random orbital sander AROS-B 150NV, Type: AROS-B****Order data**

Order number	077325 AROS-B
GTIN	6416868940206
Item class	07E

Description**Version:**

Brushless cordless spot repair sander with 5.0mm stroke for flexible cordless machining. For wet and dry grinding. Optimum ergonomic design.

- **Quick disc change due to Quick-Lock system.**
- **Up to 16 hours operating time for industrial applications.**
- **Quick battery charge time 45 min.**
- **Low noise level and low vibration level.**

Supplied with:

2 × 10.8 V / 2.5 Ah battery, charger and 32 mm backing pad.

Note:

Suitable grinding discs can be found under No. 567803 and No. 567902 in Group 56.

Technical description

Operating noise	62 dB
maximum vibration to EN	1.9 m/s ²
Stroke	5 mm
Speed	4000 - 8000 min ⁻¹
Battery voltage	10.8 V

Battery capacity	2.5 Ah
maximum diameter	32 mm
Manufacturer's designation	AROS-B 150NV
Power supply	Rechargeable battery-powered
Weight	0.6 kg
Series	AROS
Type of product	Orbital sander

Accessories

Velour-backed abrasive disc ABRANET® Grit 240	567803 240
Velour-backed abrasive disc ABRANET® Grit 400	567803 400
ABRALON™ disc Grit 2000	567902 2000
ABRALON™ disc Grit 360	567902 360
ABRALON™ disc Grit 500	567902 500
ABRALON™ disc Grit 1000	567902 1000
ABRALON™ disc Grit 4000	567902 4000
Velour-backed abrasive disc ABRANET® Grit 320	567803 320
Velour-backed abrasive disc ABRANET® Grit 180	567803 180
Velour-backed abrasive disc ABRANET® Grit 80	567803 80
Velour-backed abrasive disc ABRANET® Grit 120	567803 120