



Aluminium stepladder, with rungs, double-sided access, Number of rungs: 2X10



Order data

Order number	966053 2X10
GTIN	4031405330207
Item class	98G

Description

Version:

Stiles of rectangular hollow section, serrated square rungs 30×30mm, permanently swaged to the stiles, tapered stiles for stability. Upper ends of the stile fitted with end caps. nivello® non-slip ladder end caps. 2 high-strength Perlon straps to prevent splaying ensure high stability, transport security clips. Galvanised steel hinges with screw attachment.

Standard:

DIN EN 131.

Technical description

Weight	13.3 kg
outer width at bottom	0.65 m
Type of step	Rung
Accessibility	double-sided
Rung/step depth	30 mm

Working height approx.	3.3 m
Ladder length	2.95 m
Ladders and platforms load capacity	150 kg
Type of product	Stepladder