



## Aluminium stepladder, with rungs, double-sided access, Number of rungs: 2X6



### Order data

Order number	966053 2X6
GTIN	4031405330122
Item class	98G

### Description

#### Version:

Stiles of rectangular hollow section, serrated square rungs 30×30mm, permanently swaged to the stiles, tapered stiles for stability. Upper ends of the stile fitted with end caps. nivello® non-slip ladder end caps. 2 high-strength Perlon straps to prevent splaying ensure high stability, transport security clips. Galvanised steel hinges with screw attachment.

#### Standard:

**DIN EN 131.**

### Technical description

Ladder length	1.83 m
Type of step	Rung
Rung/step depth	30 mm
outer width at bottom	0.53 m
Weight	7.7 kg

Accessibility	double-sided
Working height approx.	3.3 m
Ladders and platforms load capacity	150 kg
Type of product	Stepladder