



GÜNZBURGER STEIGTECHNIK

## Aluminium stepladder, with rungs, double-sided access, Number of rungs: 2X8



### Order data

Order number	966053 2X8
GTIN	4031405330160
Item class	98G

### Description

#### Version:

Stiles of rectangular hollow section, serrated square rungs 30×30mm, permanently swaged to the stiles, tapered stiles for stability. Upper ends of the stile fitted with end caps. nivello® non-slip ladder end caps. 2 high-strength Perlon straps to prevent splaying ensure high stability, transport security clips. Galvanised steel hinges with screw attachment.

#### Standard:

**DIN EN 131.**

### Technical description

Rung/step depth	30 mm
Ladder length	2.4 m
Accessibility	double-sided
Weight	9.8 kg
outer width at bottom	0.59 m

Working height approx.	3.8 m
Type of step	Rung
Ladders and platforms load capacity	150 kg
Type of product	Stepladder