



Hand-held core drilling machine, Type: 72710361



Order data

Order number	075130 72710361
GTIN	4014586876023
Item class	03F

Description

Version:

Hand-held 2-speed metal core-drilling system, for up to 6× quicker drilling progress when core drilling.

- **Stepless, electronically controlled speed.**
- **QuickIN PLUS drill chuck for changeover without tools.**
- **Use with low applied force.**
- **Safe handling due to torque slip clutch.**
- **Drilling up to 80 mm in steel with a carbide hole saws.**
- **Drilling up to 25 / 30 mm in steel / aluminium with carbide core drills.**
- **QuickIN PLUS drill chuck for changeover without tools.**

Advantage:

2-speed metal core drilling system.

Supplied with:

Supplied with quick-clamping drill chuck Ø 3 – 16 mm, extra handle, centre drill, cutting spray, and tool case.

Note:

See No. 075132 for suitable carbide core drills.

TiAlN-coated carbide core drills, carbide hole saws, and carbide hole saws for pipes are available on request.

Packaging: Carrying case

Manufacturer's designation: KBH 25-2U

Power consumption: 1200 W

Speed range 1st speed: 0 - 520 rpm

Speed range 2nd speed: 0 - 1600 rpm

maximum drill Ø in steel: 25 mm

Tool arbor shape: QuickIN PLUS

Technical description

Tool arbor shape	QuickIN PLUS
Manufacturer's designation	KBH 25-2U
Power consumption	1200 W
Speed range 2nd speed	0 - 1600 rpm
maximum vibration to EN	< 2.5 m/s ²
maximum drill Ø in steel	25 mm
Speed range 1st speed	0 - 520 rpm
Weight	3.4 kg
Special features	For use in restricted spaces
Power supply	Mains operated
Suitable for material	Steel
Packaging	Carrying case
Type of product	Core drilling machine

Accessories

Carbide core drills for KBH25 – 2U Hole Ø 22 mm	075132 22
Carbide core drills for KBH25 – 2U Hole Ø 16 mm	075132 16
Carbide core drills for KBH25 – 2U Hole Ø 19 mm	075132 19
Carbide core drills for KBH25 – 2U Hole Ø Z/5 mm	075132 Z/5
Carbide core drills for KBH25 – 2U Hole Ø Z/1 mm	075132 Z/1
Carbide core drills for KBH25 – 2U Hole Ø 14 mm	075132 14
Carbide core drills for KBH25 – 2U Hole Ø 23 mm	075132 23
Carbide core drills for KBH25 – 2U Hole Ø 15 mm	075132 15

Carbide core drills for KBH25 – 2U Hole Ø 21 mm	075132 21
Carbide core drills for KBH25 – 2U Hole Ø 17 mm	075132 17
Centre drill	075133
Carbide core drills for KBH25 – 2U Hole Ø 25 mm	075132 25
Carbide core drills for KBH25 – 2U Hole Ø 18 mm	075132 18
Carbide core drills for KBH25 – 2U Hole Ø 24 mm	075132 24
Carbide core drills for KBH25 – 2U Hole Ø 20 mm	075132 20