



LED cordless lamp 0 version without battery, 18 V, Type: M18SLED



Order data

Order number	073211 M18SLED
GTIN	4002395287147
Item class	07A

Description

Version:

Robust Li-Ion battery lights with high light intensity. **Robust Li-ion battery lights with TRUEVIEW™ technology.**

- **Tiltable floodlight head with up to 1,250 Lumen.**
- **Range 650 m.**
- **4 lighting levels for maximum flexibility.**

With point beam mode and floodlight mode.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Suitable for:

Milwaukee 18 V batteries (No. 073816 MB18 and 073827 MB18).

Supplied with:

Cordless lamp without battery and without charger.

Technical description

Manufacturer's designation	M18SLED-0
Battery voltage	18 V
IP Index of Protection	IP 54
Illumination step 2	1200 lm

Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Weight without battery	1000 g
Power supply	Rechargeable battery-powered
Illumination	1250 lm
Bulb	LED module
ATEX zone	no
Product name attribute	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Work lamp

Accessories

Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C