

**Cordless hand-held circular saw, Type: GKS1226****Order data**

Order number	078183 GKS1226
GTIN	3165140895217
Item class	03B

Description**Version:**

Handy 12 V / 3.0 Ah **cordless portable circular saw.**

- **The most compact design in its class, for perfect handling.**
- **Outstanding view of the line of cut, thanks to the bright LED.**
- **Excellent ergonomics: small handle circumference and light weight (only 1.4 kg) for the best comfort when working.**
- **Sturdy aluminium base plate for precise cutting.**
- **Dust extraction adapter compatible with the Bosch extraction system.**

Supplied with:

Supplied with charger, saw blade for wood, parallel stop / guide rail adapter, extraction adapter, hexagon L-wrench and L-BOXX 238.

Note:

Circular saw blades can be found under 583920.

See from No. 073851 and No. 073866 for suitable spare batteries and chargers.

Technical description

Weight	1.4 kg
Packaging	Modular case (L-Boxx)
Battery capacity	3 Ah

Version	Hand-held circular saw
Manufacturer's designation	GKS12V-26
Saw blade Ø	85 mm
maximum vibration to EN	< 2.5 m/s ²
suitable battery - supplier / battery type / voltage	Bosch 12 V
Saw blade bore Ø	15 mm
maximum speed	1400 min ⁻¹
Battery voltage	12 V
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
maximum cutting depth	26.5 mm
Power supply	Rechargeable battery-powered
Type of product	Saw

Accessories

Li-ion battery Battery type, battery voltage B12 V	073855 B12
Circular saw blade, wood, alternating teeth Blade Ø D 85 mm	583950 85
Battery charger Type GAL1240	073866 GAL1240