



Jigsaw, Type: GST25M



Order data

Order number	078200 GST25M
GTIN	3165140584661
Item class	03B

Description

Version:

Bosch jigsaw with Bosch SDS System for simple cutting blade change, no tools required. Jigsaw with **D-shape handle** especially suitable for **sawing metal**. Short stroke for a smooth cutting action. With 2-step blade swing and electronic controls.

Supplied with:

Including 15-piece saw blade set for metal, aluminium and stainless steel, chip break guard, offset screwdriver, carrying case.

Note:

Suitable spare batteries and chargers can be found under No. 073808 – 073840.

Packaging: Carrying case

Manufacturer's designation: GST 25 metal

Power consumption: 670 W

Rate of strokes: 500 - 2600 rpm

maximum sawn thickness steel: 15 mm

maximum sawn thickness wood: 80 mm

Orbital stroke: 2-way

Technical description

suitable jigsaw blades	588400 – 588551
------------------------	-----------------

Power consumption	670 W
maximum sawn thickness steel	15 mm
Special features	Metal jigsaw
Length	265 mm
Orbital stroke	2-way
maximum sawn thickness wood	80 mm
Manufacturer's designation	GST 25 metal
Height	206 mm
Cable length	2.3 m
Rate of strokes	500 - 2600 rpm
maximum vibration to EN	3.5 m/s ²
tool change without tools	yes, SDS system
Weight	2.7 kg
Packaging	Carrying case
Format	D-shape handle
Power supply	Mains operated
Type of product	Saw