



Aluminium multi-purpose ladder, 4-part, with crossbar base, Number of rungs: 14



Order data

Order number	966105 14
GTIN	4031405313149
Item class	98G

Description

Version:

Lean-to ladder, stepladder, and work platform all in one. When used as a work platform, a walkboard and railing are necessary (please request these from us separately). 6 automatically locking steel hinges ensure operating safety. Rung spacing 280mm. Safe working and high operating safety due to 2 nivello® crossbar bases and non-slip nivello® end caps. The crossbar bases are supplied loose and are fixed to the bottom of the stiles with two bolts each.

Standard:

DIN EN 131.

Note:

For these ladders, you will receive the cross beams specified in the standard.

Technical description

Depth closed	0.25 m
Ladder length extended	4.2 m
Width closed	1.23 m

Number of steps	2×3 + 2×4
Stepladder working height approx.	5.3 m
Cross-span width	0.93 m
Weight	15 kg
Length closed	0.35 m
Ladder length as a stepladder	2.02 m
Height as a work platform	0.99 m
Ladders and platforms load capacity	150 kg
Type of product	Multi-purpose ladder