



## Aluminium multi-purpose ladder, 4-part, with crossbar base, Number of rungs: 12



### Order data

Order number	966105 12
GTIN	4031405313125
Item class	98G

### Description

#### Version:

Lean-to ladder, stepladder, and work platform all in one. When used as a work platform, a walkboard and railing are necessary (please request these from us separately). 6 automatically locking steel hinges ensure operating safety. Rung spacing 280mm. Safe working and high operating safety due to 2 nivello® crossbar bases and non-slip nivello® end caps. The crossbar bases are supplied loose and are fixed to the bottom of the stiles with two bolts each.

#### Standard:

**DIN EN 131.**

#### Note:

For these ladders, you will receive the cross beams specified in the standard.

### Technical description

Number of steps	4×3
Width closed	0.99 m
Length closed	0.35 m

Stepladder working height approx.	4.8 m
Ladder length extended	3.65 m
Weight	14 kg
Cross-span width	0.93 m
Depth closed	0.25 m
Ladder length as a stepladder	1.76 m
Height as a work platform	0.99 m
Ladders and platforms load capacity	150 kg
Type of product	Multi-purpose ladder