



Angle grinder GWS, Type: 19-125CIE



Order data

Order number	077109 19-125CIE
GTIN	3165140838382
Item class	03C

Description

Version:

Very powerful 1900 W angle grinder for maximum productivity and very good user protection

- **Long working life due to motors with direct motor cooling, constant-speed electronics, overload protection and long-life carbon brushes.**
- **Easy to use due to slim body with Softgrip surface for a secure grip.**
- **Additional handle for 40 % reduction in vibration, ensuring non-fatiguing working (EN 60745).**
- **Top user protection due to kick-back stop, restart inhibit, torsion-resistant protective hood and reduced vibration.**

1900 W motor with electronic speed control.

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Technical description

Length	311 mm
maximum cutting depth	34 mm
Power consumption	1900 W
maximum disc Ø	125 mm

Kick-back stop	yes
Weight	2.4 kg
maximum vibration to EN	6 m/s ²
Manufacturer's designation	GWS 19-125 CIE
Special features	Electronic speed control
Restart block	yes
Height	103 mm
Speed range	2800 - 11500 min ⁻¹
Power supply	Mains operated
Type of product	Angle grinder