

Garant**Digital height gauge and marking-out system with data output, Marking height: 600mm****Order data**

Order number	444000 600
GTIN	4045197889836
Item class	41F

Description**Version:**

Strong base with ground standing surface and dirt trap grooves. Ergonomic and comfortable plastic cap with Santoprene® surface. Flat carbide-tipped scriber for easy marking out even in narrow grooves, exchangeable. Fold-away or removable protection cap for injury-free working. Marking out from 0, drawing dimensions can therefore be transferred directly without the risk of calculation errors. Very easy to read, high-contrast 11 mm-high LCD display. Incl. data output. With fine adjustment and locking screw.

Version of the advertising text:

Strong base with ground standing surface and dirt trap grooves. Ergonomic and comfortable plastic cap with Santoprene® surface. Flat carbide-tipped scriber for easy marking out even in narrow grooves, exchangeable, marking out from 0. Drawing dimensions can therefore be transferred directly without the risk of calculation errors. Fold-away or removable protection cap for injury-free working. With fine setting adjustment and high-speed screw. Very easy to read, high-contrast 11 mm-high LCD display. Incl. data output.

Function:

- **Zeroing in any position**
- **Preset**
- **Selectable mm / inches**

- **Data output RS232 Proximity**
- **Hold function**

Supplied with:

Scriber No. 444010 size 75.

Battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948.

Technical description

Scale divisions	0.0005 in
Column cross section	30×12 mm
Scale divisions	0.01 mm
Base width	110 mm
Marking height	600 mm
Base length	165 mm
Error limit	0.05 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Height of numerals	11 mm
Interface	USB interface
Interface	RS232C interface
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device

Services

CalibrationHeight gauge / height scriber maximum
measuring range 1000 mm

024630 1000

Accessories

Connection cable Type USB2	498948 USB2
Connection cable Type R2	498948 R2
Spare scriber, carbide tipped Length 150 mm	444010 150
Button cell / special battery Battery type CR2032	081560 CR2032
Spare scriber, carbide tipped Length 75 mm	444010 75