

Garant**Digital height gauge and marking-out system with data output, Marking height: 300mm****Order data**

Order number	444000 300
GTIN	4045197889829
Item class	41F

Description**Version:**

Strong base with ground standing surface and dirt trap grooves. Ergonomic and comfortable plastic cap with Santoprene® surface. Flat carbide-tipped scriber for easy marking out even in narrow grooves, exchangeable. Fold-away or removable protection cap for injury-free working. Marking out from 0, drawing dimensions can therefore be transferred directly without the risk of calculation errors. Very easy to read, high-contrast 11 mm-high LCD display. Incl. data output. With fine adjustment and locking screw.

Version of the advertising text:

Strong base with ground standing surface and dirt trap grooves. Ergonomic and comfortable plastic cap with Santoprene® surface. Flat carbide-tipped scriber for easy marking out even in narrow grooves, exchangeable, marking out from 0. Drawing dimensions can therefore be transferred directly without the risk of calculation errors. Fold-away or removable protection cap for injury-free working. With fine setting adjustment and high-speed screw. Very easy to read, high-contrast 11 mm-high LCD display. Incl. data output.

Function:

- **Zeroing in any position**
- **Preset**
- **Selectable mm / inches**

- **Data output RS232 Proximity**
- **Hold function**

Supplied with:

Scriber No. 444010 size 75.

Battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948.

Technical description

Column cross section	30×12 mm
Scale divisions	0.0005 in
Scale divisions	0.01 mm
Base width	110 mm
Error limit	0.04 mm
Marking height	300 mm
Base length	165 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Height of numerals	11 mm
Interface	USB interface
Interface	RS232C interface
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device

Services

CalibrationHeight gauge / height scriber maximum
measuring range 300 mm

024630 300

Accessories

Spare scriber, carbide tipped Length 75 mm	444010 75
Button cell / special battery Battery type CR2032	081560 CR2032
Connection cable Type R2	498948 R2
Connection cable Type USB2	498948 USB2
Spare scriber, carbide tipped Length 150 mm	444010 150