

Ansell**Pair of gloves HyFlex® 11-840, Glove size: 11****Order data**

Order number	094264 11
GTIN	10076490475588
Item class	04P

Description**Version:**

HyFlex® 11-840. Very good balance between robust abrasion-resistance, increased comfort and greater freedom of movement, thus ideal for different types of work. **Silicone-free**, thus avoiding contamination of metal parts with silicone particles. Particularly suitable for the assembly of small and medium-sized components, general use.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	11
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	12

Glove characteristics	Silicone-free
Glove characteristics	Foodstuffs certified
Glove characteristics	free of latex
Glove characteristics	Suitable for allergy sufferers
EN 388	4131A
EN 407	X1XXXX
Backing material	Nylon Spandex
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Precision
Length	200 mm
Colour	black / grey
Weight	11,6 g
Knitted technology	15G
Standard	EN 407
Application	reusable
Material	Nitrile foam
Cut protection class	A
Type of product	Multi-purpose gloves