

Garant**Precision vernier height gauge with magnifying glass, Marking height: 300mm****Order data**

Order number	443450 300
GTIN	4045197889904
Item class	41F

Description**Version:**

Strong base with ground standing surface and dirt trap grooves. Ergonomic and comfortable plastic cap with Santoprene® surface. Parallax-free reading with fine, high-contrast scale.

Additional magnifying glass for optimum legibility. All reading parts are anti-glare satin chrome-plated. With fine setting adjustment and high-speed screw. Flat carbide-tipped scriber for easy marking out even in narrow grooves, exchangeable, marking out from 0. Drawing dimensions can therefore be transferred directly without the risk of calculation errors. Fold-away or removable protection cap for injury-free working.

Version of the advertising text:

Strong base with ground standing surface and dirt trap grooves. Ergonomic and comfortable plastic cap with Santoprene® surface. Flat carbide-tipped scriber for easy marking out even in narrow grooves, exchangeable, marking out from 0. Drawing dimensions can therefore be transferred directly without the risk of calculation errors. Fold-away or removable protection cap for injury-free working. With fine setting adjustment and high-speed screw.

Additional magnifying glass for optimum legibility. All reading parts are non-glare satin chrome-plated.

Supplied with:

Scriber No. 444010 size 75.

Technical description

Marking height	300 mm
Error limit	0.05 mm
Base length	165 mm
Column cross section	30×12 mm
Vernier	1/50 mm
Base width	110 mm
Calibration	E1
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Height gauge and marking device

Services

CalibrationHeight gauge / height scriber maximum measuring range 300 mm	024630 300
DAkkS calibrationHeight gauge / height scriber maximum measuring range 300 mm	024640 300

Accessories

Spare scriber, carbide tipped Length 75 mm	444010 75
--------------------------------------------	-----------