



Cordless single-speed drill, Type: 71050262



Order data

Order number	075012 71050262
GTIN	4014586881751
Item class	03F

Description

Version:

- **Cordless power drill with high concentricity for precise drilling results.**
- **Maintenance-free brushless FEIN PowerDrive motor, fully enclosed and dust-proof with high efficiency and very long working life.**
- **Röhmm metal quick-release chuck with automatic spindle locking pin.**
- **Self-tightening chuck clamping jaws.**
- **High-strength metal gearbox casing with 43 mm Ø clamping neck, width across the head only 23 mm.**
- **Outstanding ergonomics with Fein sensitive handle for non-tiring long-time use.**

Single-speed power drill for drilling up to 10 mm in steel, speed under load 1100 rpm.

Advantage:

Outstanding ergonomics.

Supplied with:

Quick-clamping drill chuck with clamping force safety device, 1 additional handle. **Select version without rechargeable battery and charger.**

Note:

Suitable rechargeable battery starter set available with No. 073832 92604324.

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: ABOP 10 select

Battery voltage: 18 V

Speed range: 0 - 1250 rpm

Drill chuck adapter: 1/2 inch – 20 UNF
 Chuck clamping range: 1.5 - 13 mm
 maximum twist drill size Ø in steel: 10 mm

Technical description

Battery voltage	18 V
Speed range	0 - 1250 rpm
Weight	1.5 kg
maximum twist drill size Ø in steel	10 mm
Drill chuck adapter	1/2 inch – 20 UNF
Chuck clamping range	1.5 - 13 mm
Manufacturer's designation	ABOP 10 select
maximum vibration to EN	< 2.5 m/s ²
maximum twist drill size Ø in wood	30 mm
Reversible	yes
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Type of product	Drill

Accessories

Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Battery charger Type FE30	073845 FE30
Battery charger Type FE50	073845 FE50
Li-ion battery Battery type, battery voltage FE18 V	073838 FE18
Battery charger Type FE80	073845 FE80