

**Pair of gloves FlexMech® 663, Glove size: 11****Order data**

| | |
|--------------|---------------|
| Order number | 094255 11 |
| GTIN | 4008198766315 |
| Item class | 04Q |

Description**Version:**

FlexMech® 663. The glove has high abrasion resistance and good ergonomic fit. Outstanding touch sensitivity, with high breathability. **Silicone-free** and washable.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|----------------------------|-----------------------|
| Manufacturer's designation | FlexMech 663 |
| Glove size | 11 |
| Series | FlexMech® |
| Type of glove | Multi-purpose gloves |
| Protection category | Category II |
| Clothing standard | Oeko-Tex Standard 100 |

| | |
|-----------------------|------------------------|
| Contents | 11 |
| Glove characteristics | Silicone-free |
| Glove characteristics | DMF-free |
| EN 388 | 4131X |
| EN 407 | X1XXXX |
| Backing material | Polyamide |
| Coating | Nitrile foam |
| Coating variant | The palms of the hands |
| Application range | Precision |
| Length | 240 - 260 mm |
| Colour | black / grey |
| Weight | 54 g |
| Knitted technology | 15G |
| Standard | EN 407 |
| Contact heat up to | 100 °C |
| Application | reusable |
| Cut protection class | 1 |
| Type of product | Multi-purpose gloves |