

Ansell**Pair of gloves HyFlex® 11-925, Glove size: 11****Order data**

Order number	094248 11
GTIN	10076490458680
Item class	04P

Description**Version:**

HyFlex® 11-925. Glove with **18-gauge knitted fabric** and double coating of nitrile and nitrile foam for an excellent combination of high touch sensitivity, secure grip in oily conditions and good skin protection. A newly developed grip technology reduces the risk of objects slipping out of your hand in dynamic working areas. Particularly suitable for sorting and testing lightweight parts, assembly of oily parts, loading and unloading production belts, maintenance work.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	11
Series	HyFlex®
Protection category	Category II
Type of glove	Multi-purpose gloves

Contents	12
Glove characteristics	Silicone-free
Glove characteristics	free of latex
EN 388	3111A
Backing material	Spandex nylon
Coating	Nitrile
Coating variant	3/4 coating
Application range	Precision
Length	205 mm
Colour	blue
Weight	17.5 g
Knitted technology	18G
Application	reusable
Material	Nitril
Cut protection class	A
Type of product	Multi-purpose gloves