

uvex**Pair of gloves uvex phynomic XG, Glove size: 8**

Order data

Order number	094407 8
GTIN	4048612036631
Item class	04W

Description

Version:

uvex phynomic XG. The nitrile foam coating with uvex Xtra Grip technology ensures an unusually good grip in oily conditions combined with good breathability. Despite its robustness and abrasion-resistance, the glove is characterised by a low weight and good flexibility.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	8
Series	uvex phynomic
Type of glove	Multi-purpose gloves
Protection category	Category II
Clothing standard	Oeko-Tex Standard 100

EN 388	4121X
Backing material	Recycled polyamide, elastane, carbon
Coating	Nitrile
Coating variant	The palms of the hands
Application range	All-round
Application range	Precision
Colour	black / anthracite
Weight	35 g
Application	reusable
Type of product	Multi-purpose gloves