

Ansell**Pair of gloves ActivArmr Hycron® 27-805, Glove size: 10****Order data**

Order number	094431 10
GTIN	10076490484085
Item class	04P

Description**Version:**

ActivArmr Hycron® series. **Hard-wearing gloves** of jersey cotton with nitrile coating for the most demanding applications. High resistance to sharp-edged and chafing materials. Robust and more flexible than PVC, three times longer service life than heavy leather gloves. **Effective barrier against greases and oils.** Particularly suitable for rough castings, moulded plastic parts, steel bar, sheet metal, high-tensile cable, building materials, unfinished wood. With safety cuff and full coating.

Standard:

EN 388; EN ISO 21420

Antistatisch gemäß EN 1149.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	10
Series	Hycron®
Type of glove	Multi-purpose gloves

Protection category	Category II
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	free of latex
EN 388	4121B
Backing material	Cotton
Coating	Nitrile
Coating variant	Full coating
Application range	Heavy Duty
Length	256 mm
Colour	blue
Weight	69 g
Application	reusable
Material	Nitril
Cut protection class	B
Type of product	Multi-purpose gloves