

**uvex****Pair of gloves uvex phynomic XG, Glove size: 9**

## Order data

|              |               |
|--------------|---------------|
| Order number | 094407 9      |
| GTIN         | 4048612036648 |
| Item class   | 04W           |

## Description

**Version:**

uvex phynomic XG. The nitrile foam coating with uvex Xtra Grip technology ensures an unusually good grip in oily conditions combined with good breathability. Despite its robustness and abrasion-resistance, the glove is characterised by a low weight and good flexibility.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

## Technical description

|                     |                       |
|---------------------|-----------------------|
| Glove size          | 9                     |
| Series              | uvex phynomic         |
| Protection category | Category II           |
| Type of glove       | Multi-purpose gloves  |
| Clothing standard   | Oeko-Tex Standard 100 |

|                   |                                      |
|-------------------|--------------------------------------|
| EN 388            | 4121X                                |
| Backing material  | Recycled polyamide, elastane, carbon |
| Coating           | Nitrile                              |
| Coating variant   | The palms of the hands               |
| Application range | All-round                            |
| Application range | Precision                            |
| Colour            | black / anthracite                   |
| Weight            | 35 g                                 |
| Application       | reusable                             |
| Type of product   | Multi-purpose gloves                 |