

**Pair of gloves RewoMech 641, Glove size: 10****Order data**

Order number	094377 10
GTIN	4008198764106
Item class	04Q

Description**Version:**

RewoMech 641. **Wear-resistant synthetic leather** for protection during mechanical work. The glove provides excellent grip, even with wet components, and it protects the palm from oil and water with a moisture barrier made of Tyvek®. The cuff has a hook and loop fastener. The glove is breathable and is an alternative to conventional leather gloves. Particularly suitable for metal and plastic processing, precision mechanics, assembly and transport work.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	10
Manufacturer's designation	RewoMech 641
Protection category	Category II
Type of glove	Multi-purpose gloves

Contents	12
Glove characteristics	DMF-free
Glove characteristics	Hook & loop fastener
Glove characteristics	free of latex
EN 388	2121X
Backing material	Synthetic leather
Application range	All-round
Length	240 - 260 mm
Colour	grey / black
Weight	90 g
Application	reusable
Cut protection class	1
Type of product	Multi-purpose gloves