

LESSMANN
THE GERMAN BRUSH COMPANY**Knotted end brush Stainless steel wire, Brush \varnothing D1 \times bristle thickness:
19X0,35mm****Order data**

Order number	574900 19X0,35
GTIN	4017359126295
Item class	57L

Description**Version:**

Smooth, knotted wire, crimped into steel ferrule, **shank \varnothing 6 mm**, even density, extremely wear-resistant.

Stainless wire quality 1.4401 (AISI 316). Carrier body with plastic sheathing for machining stainless steel.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

Technical description

maximum speed	20000 min ⁻¹
Number of twisted knots	6
Length of brush section H ₁	28 mm
Brush \varnothing D ₁	19 mm
Bristle thickness	0.35 mm
Shank \varnothing D _s	6 mm
Brush material	Stainless steel wire
Twisted knotting	left-hand plait

Type of product

End brush