

LESSMANN®
THE GERMAN BRUSH COMPANY**End brush Stainless steel wire 0.30 mm, Type: 10X20****Order data**

Order number	574600 10X20
GTIN	4017359006801
Item class	57L

Description**Version:**

Waved special high quality wire, crimped into steel ferrule, **shank Ø 6 mm.**

Application:

For straight die grinders, on flexible drive machines and drills. For cleaning and deburring at inaccessible places.

Technical description

maximum speed	20000 min ⁻¹
Clamp length L ₂	20 mm
Length of brush section H ₁	20 mm
Clamp Ø D ₂	10 mm
Brush Ø D ₁	12 mm
Overall length L	60 mm
Type of product	End brush