

**Pair of gloves 03440, Glove size: 10****Order data**

Order number	094424 10
GTIN	4059904105621
Item class	09H

Description**Version:**

Robust gloves of jersey cotton with nitrile coating for medium and heavy applications. Significantly longer life than heavy leather gloves, and robust and more flexible than PVC gloves. Effective barrier against greases and oils. Particularly suitable for rough castings, moulded plastic parts, steel bar, sheet metal, high-tensile cable, building materials, unfinished wood. 03440. With safety cuff and full coating.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	10
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	12

EN 388	4221X
Backing material	Cotton
Coating	Nitrile
Coating variant	Full coating
Application range	Heavy Duty
Colour	blue / natural
Application	reusable
Type of product	Multi-purpose gloves