

LESSMANN®
THE GERMAN BRUSH COMPANY**Tube brush micro-abrasive (SiC) 1000 grit, Brush Ø D1: 2,2mm****Order data**

Order number	574476 2,2
GTIN	4017359335260
Item class	57L

Description**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles.

Fine silicon carbide bristles (**SiC**) in **1000grit**, brush Ø **0.25mm**, overall length 100mm.

Application:

Abrasive nylon brushes work at both the tips and the sides of the bristles. The continued exposure of new abrasive material ensures an **even abrasive effect**. For **deburring** (cross) bores, O-ring recesses, and for **cleaning** and **polishing** nozzles and small hydraulic bores.

Technical description

Brush Ø D ₁	2.2 mm
Working length L ₃	18 mm
Shank Ø D _s	0.9 mm
Type of product	Tube brush