

**Pair of gloves with raised dots, Glove size: 10****Order data**

| | |
|--------------|---------------|
| Order number | 094301 10 |
| GTIN | 4045197890177 |
| Item class | 02H |

Description**Version:**

Breathable assembly glove with innovative, water-based PU-nitrile coating for the highest level of precision, flexibility and dexterity in dry and slightly oily working environments. Particularly finely structured surface due to intensive finishing process. Long life through very high abrasion resistance. DMF-free.

With **additional nitrile dots** for better grip and longer service life.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|---------------------|-----------------------|
| Glove size | 10 |
| Type of glove | Multi-purpose gloves |
| Protection category | Category II |
| Clothing standard | Oeko-Tex Standard 100 |

| | |
|-----------------------|--|
| Contents | 12 |
| Glove characteristics | DMF-free |
| Glove characteristics | Suitable for allergy sufferers |
| EN 388 | 4131X |
| Backing material | Lycra®, polyamide |
| Coating | water-based PU/nitrile |
| Coating variant | The palms of the hands |
| Application range | All-round |
| Application range | Precision |
| Length | 255 mm |
| Colour | black / grey |
| Knitted technology | 15G |
| AQL | G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor. |
| Application | reusable |
| Type of product | Multi-purpose gloves |