

Plug gauge A-ZC 6-13, Nominal size Ø: 66mm



Order data

Order number	484020 66
GTIN	2050001952172
Item class	48B

Description

Version:

The "Go" ends of these working gauges have a **wear allowance** to DIN 7164. Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped. "Go" / "No Go" plug gauges for ISO **tolerance bands A – ZC** in **basic tolerance qualities 6 – 13**.

Standard:

Toleranz und Abmaße nach **DIN EN ISO 1938-1, DIN 2245-1 und DIN 7164**.

Note:

- **Further intermediate sizes available on request or can simply be ordered at www.hoffmann-group.com, for instance No. 484000 size 82.**
- **For acceptance gauges (without wear allowance) see No. 484027.**
- **For gauges with intermediate sizes and all Ø with numeric tolerances see No. 484025.**
- **Specify required tolerance class. When ordering please state the tolerance band (A–ZC) and basic tolerance quality (6–13), e.g. No. 484020 10F10.**

Technical description

Tolerance zone	ZB
Tolerance zone	JS
Tolerance zone	T
Tolerance zone	E
Tolerance zone	X
Tolerance zone	FG
Tolerance zone	N
Tolerance zone	B

Tolerance zone	ZC
Tolerance zone	K
Tolerance zone	U
Tolerance zone	EF
Tolerance zone	Y
Tolerance zone	G
Tolerance zone	P
Tolerance zone	C
Tolerance zone	Z
Tolerance zone	H
Tolerance zone	R
Tolerance zone	CD
Tolerance zone	ZA
Tolerance zone	J
Tolerance zone	S
Tolerance zone	D
Tolerance zone	V
Tolerance zone	F
Tolerance zone	M
Tolerance zone	A
Standard	DIN 7164
Standard	DIN 2245-1
Standard	DIN EN ISO 1938-1
Quality	9
Quality	6
Quality	13
Quality	10
Quality	8
Quality	7

Quality	12
Quality	11
Type of gauge	"Go" plug gauge
Type of gauge	"No Go" gauge
Nominal size	66 mm
Calibration	M2
Type of product	Pug Gauge

Services

DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 200 mm	028340 200
Calibration "Go" / "No Go" plug gauge maximum \varnothing 200 mm	028300 200