

LESSMANN®
THE GERMAN BRUSH COMPANY

Knotted end brush Stainless steel wire, Brush Ø D1× bristle thickness: 22X0,25mm



Order data

Order number	574900 22X0,25
GTIN	4017359071441
Item class	57L

Description

Version:

Smooth, knotted wire, crimped into steel ferrule, **shank Ø 6 mm**, even density, extremely wear-resistant.

Stainless wire quality 1.4401 (AISI 316). Carrier body with plastic sheathing for machining stainless steel.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

Technical description

Bristle thickness	0.25 mm
Length of brush section H ₁	28 mm
Brush Ø D ₁	22 mm
maximum speed	20000 min ⁻¹
Number of twisted knots	8
Shank Ø D _s	6 mm
Brush material	Stainless steel wire
Twisted knotting	left-hand plait

Type of product

End brush