

Interior brush NOVOFLEX-B SiC180 grit, Type: 8



Order data

Order number	574495 8
GTIN	4013349527349
Item class	57L

Description

Version:

Self-centring interior brush with flexible bristles carrying **silicon carbide spheres**. Overall length 200 mm.

Application:

For **chamfering, finishing of surfaces** and **honing**. Generates **fine evenly ground surface** with high contact area. For use in power drills and fixed drills. Recommended speed 350 – 700 rpm, contact time 20 – 40 seconds.

Note:

Do not use dry, use with cutting oil No. 084205.

Technical description

Brush $\varnothing D_1$	9 mm
suitable for bore \varnothing	7.1 - 8 mm
Working length L_3	50 mm
Shank $\varnothing D_s$	3.6 mm
Series	NOVOFLEX-B
Brush material	Silicon carbide
Grinding medium code	SiC
Grit	180
recommended speed	350 - 700 min ⁻¹
Type of product	Internal brush

Accessories

High-performance cutting oil free of mineral oilUV 80
Contents 5 l

084205 5

High-performance cutting oil free of mineral oilUV 80
Contents 20 l

084205 20

High-performance cutting oil free of mineral oilUV 80
Contents 0,25 l

084205 0,25