

## Rigid load arm, Base length in m / safe working load in t: 2,4/1



### Order data

Order number	919973 2,4/1
GTIN	4052462012745
Item class	94B

### Description

#### Version:

Load arms increase the reach of the fork-lift truck. Sturdy steel construction with fork insertion slots for fork tines. Also suitable for clamp trucks. Chain protection against accidental slippage and a swivel hook. Rigid design with 3 available hook positions.

#### Colour:

Optional **paint finishes** RAL 5012, Light blue, RAL 2000 Yellow orange, RAL 3000 Fire red, RAL 6011 Reseda green, RAL 7005 Mouse grey.

#### Note:

Comply with the load capacity of the fork lift truck!

### Technical description

Width	600 mm
Base length	2400 mm
Internal dimension at intake: width	220 mm
Load capacity of the outermost eye	100 kg
maximum load capacity	1000 kg
Weight	49 kg
Internal dimension at intake: height	80 mm
Fork-lift fork socket pitch	160 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005

Type of product

Load arm